



## 17" AND 19" LED-BACKLIT LCD DRAWERS

IT or lab administrators often need fast and reliable at-the-rack access to their servers for deployment, administration, and maintenance activities. Raritan's 1U modular LED drawers, with LED-backlit LCD displays provide both energy savings and consolidated access to multiple servers from a single location.

## ONE WORKSTATION FOR SERVER ACCESS AND CONTROL

When connecting to your existing analog or digital KVM switches, Raritan's LED consoles combine video, keyboard, and touchpad functionality to manage a rack, or multiple racks of servers from a single workstation.

They also include built-in USB 2.0 ports for convenient, front-of-the-rack media connections to keyboard, mouse, and smart card readers to manage Raritan KVM switches directly from the racks in which they are installed.

### FEATURES AND BENEFITS

- DVI-D and VGA video inputs make it perfect for use with the Dominion<sup>®</sup> KX III.
- LED-backlighting provides up to 20-50% energy savings over current LCD technology.
- Accurate image rendering and video performance for sharp, clear pictures.
- Space saving 1U design for 85% less space.
- Supports DDC, DDC2, DDC2B.
- USB 2.0 pass thru port to connect external devices e.g. a smart card reader.
- Auto power on/off when opening and closing the monitor below a 20 degree angle.
- Support for Windows<sup>®</sup>, Linux<sup>®</sup> and other operating systems.



### T1700-LED

17-inch LED-backlit LCD, 16:9 screen aspect ratio, resolution support up to 1920x1080 @60 Hz.



### T1900-LED

19-inch LED-backlit LCD, 4:3 screen aspect ratio, resolution support up to 1280x1024 @75 Hz.

Model	T1700-LED	T1900-LED
Dimensions	[L] 569 x [W] 434 x [H] 43.5 mm; 17.1" x 22.4" x 1.71"	
Weight	12 Kg, 26.46 lbs	12.6 Kg, 27.78 lbs
Form Factor	1U rack mount	
KVM Cable	6 ft. combo KVM cable (VGA, PS/2, and USB) for VGA video input, keyboard and touchpad	
DVI Video Cable	6 ft. male to male DVI video cable (DVI-D, single link)	
USB Port	USB 2.0 pass thru port on front of unit to connect external devices	
Power and Heat Dissipation	Auto-Sensing 100 to 240VAC, MAX 50 / 60 Hz, 1A, 12.2 Watts, 10.5 KCAL	Auto-Sensing 100 to 240VAC, MAX 50 / 60 Hz, 1A, 16.2 Watts, 14 KCAL
<b>Video</b>		
Display Size	17.3" TFT	19" TFT
Panel Type	Active Matrix TFT LCD with LED backlight unit	
Max. Resolution Support	1920x1080 @60 Hz [Full HD 1080P]	1280x1024 @75 Hz
DDC Support	DDC / DDC2 / DDC2B	
Contrast Ratio	650:1	1000:1
Brightness (cd/m <sup>2</sup> )	300 nits	250 nits
Supported Colors	16.7 Million	
Multi-Platform	Supports DVI-D, VGA, USB and/or PS/2	
<b>Keyboard</b>		
Keyboard/ Mouse	104 Keyboard / Touchpad	
Keyboard Language Support	English, French, German, Swiss German, Italian, Japanese, Russian, Spanish, and Turkish	
<b>Environmental Specifications</b>		
Operation Temperature	0-50 °C	
Storage Temperature	-5-60 °C	
Humidity	5-90% RH, Non-Condensing	
MTBF	15,000 Hours	16,200 Hours
Altitude Specifications	Operation: 4,572 meters / Non-Operation: 9,144 meters	
Shock & Vibration	10G acceleration, peak to peak (11 ms); 1-200 Hz, 1.15 Grms random vibration	
Certifications	FCC, CE, VCCI, UL, and ROHS	
Warranty	2 years; 1 year and 2 year extended warranties are available	

Visit [www.raritan.com/rackmount-lcd-consoles](http://www.raritan.com/rackmount-lcd-consoles)  
or Call 1.800.724.8090 for more information.

©2017 Raritan Inc. All rights reserved. Raritan® is a registered trademarks of Raritan Inc. or its wholly-owned subsidiaries. All others are registered trademarks or trademarks of their respective owners. Raritan began developing KVM switches for IT professionals to manage servers remotely in 1985. Today, as a brand of Legrand, we are a leading provider of intelligent rack PDUs. Our solutions increase the reliability and intelligence of data centers in 9 of the top 10 Fortune 500 technology companies. Learn more at [Raritan.com](http://Raritan.com) V1183R2

**Raritan**  
A brand of  **legrand**