

High End PDUs Delivered in 3 Weeks

Find the Ready to Ship PDU for Your Data Center

PART NUMBER	INPUT PLUG TYPE	MAX CURRENT	FORM FACTOR	OUTLET SWITCHING	INLET METERING	OUTLET METERING	TOTAL METERING	NEMA 5-20R	C13	C19	
PX3-1749V-V2N1	CS8365C	40A	0U		✓		36		24	12	VOLTAGE: 208 V, 3-phase
PX3-5547V-V2	CS8365C	40A	0U	✓	✓	✓	24		12	12	
PX3-5666V-C5	CS8365C	35A	0U	✓	✓	✓	30		24	6	
PX3-5719V	CS8365C	35A	0U	✓	✓	✓	36		30	6	
PX3-5749V-V2	CS8365C	40A	0U	✓	✓	✓	36		24	12	
PX2-1905V-V2N1	IEC 60309 3P+E 9h 60A	48A	0U		✓		36		24	12	
PX2-1765V-V2	IEC 60309 3P+E 9h 60A	48A	0U		✓		48		48		
PX3-5551V	IEC 60309 3P+E 9h 60A	48A	0U	✓	✓	✓	24		12	12	
PX3-5905V-V2	IEC 60309 3P+E 9h 60A	48A	0U	✓	✓	✓	36		24	12	
PX2-1724V	NEMA L15-30P	24A	0U		✓		36		24	12	
PX2-1037V-01C5	NEMA L15-30P	24A	0U		✓		42		36	6	
PX2-5521	NEMA L15-30P	24A	0U	✓	✓	✓	24		24		
PX2-5525	NEMA L15-30P	24A	0U	✓	✓	✓	24		18	6	
PX3-5665V-C5	NEMA L15-30P	24A	0U	✓	✓	✓	30		24	6	
PX2-1725V	NEMA L21-30P	24A	0U		✓		36		24	12	
PX2-5520	NEMA L21-30P	24A	0U	✓	✓	✓	24		24		
PX2-5524	NEMA L21-30P	24A	0U	✓	✓	✓	24		18	6	
PX3-5522V	NEMA L21-30P	24A	0U	✓	✓	✓	24		21	3	
PX3-5660V	NEMA L21-30P	24A	0U	✓	✓	✓	30	3	21	6	
PX3-5664V-C5	NEMA L21-30P	24A	0U	✓	✓	✓	30		24	6	
PX2-1145R	NEMA 5-15P	12A	1U		✓		8	8			VOLTAGE: 120 V, single phase
PX2-2145R	NEMA 5-15P	12A	1U	✓	✓		8	8			
PX2-1146R	NEMA 5-20P	16A	1U		✓		8	8			
PX2-2146R	NEMA 5-20P	16A	1U	✓	✓		8	8			
PX2-2802	NEMA 5-20P	16A	0U	✓	✓		24	24			
PX3-5146R	NEMA 5-20P	16A	1U	✓	✓	✓	8	8			
PX3-5802V	NEMA 5-20P	16A	0U	✓	✓	✓	24	24			
PX2-1147R	NEMA L5-20P	16A	1U		✓		8	8			
PX2-2147R	NEMA L5-20P	16A	1U	✓	✓		8	8			
PX2-2475	NEMA L5-20P	16A	0U	✓	✓		24	24			
PX3-5147R	NEMA L5-20P	16A	1U	✓	✓	✓	8	8			
PX3-5475V	NEMA L5-20P	16A	0U	✓	✓	✓	24	24			
PX3TS-1147R	NEMA L5-20P (2)	16A	1U		✓		8	8			
PX2-1482	NEMA L6-20P	16A	0U		✓		24		24		VOLTAGE: 208 V, single phase
PX3-5180R	NEMA L6-20P	16A	1U	✓	✓	✓	8		8		
PX2-1497V	NEMA L6-30P	24A	0U		✓		24		20	4	
PX2-1862V-01C5	NEMA L6-30P	24A	0U		✓		42		36	6	
PX2-2496	NEMA L6-30P	24A	0U	✓	✓		24		24		
PX2-2497	NEMA L6-30P	24A	0U	✓	✓		24		20	4	
PX3-5460R-C5	NEMA L6-30P	24A	2U	✓	✓	✓	20		20		
PX3-5460V-C5	NEMA L6-30P	24A	0U	✓	✓	✓	20		20		
PX3-5464V	NEMA L6-30P	24A	0U	✓	✓	✓	20		16	4	
PX3-5496V	NEMA L6-30P	24A	0U	✓	✓	✓	24		24		
PX3-5497V-C5	NEMA L6-30P	24A	0U	✓	✓	✓	24		20	4	
PX3TS-1876R	NEMA L6-20P (2)	16A	1U		✓		9		8	1	