




IS YOUR BUSINESS EQUIPPED FOR A DISRUPTION IN IT OPERATIONS?

As a growing small or medium-sized business, the key to your success lies in being able to quickly and effectively react to situations that disrupt your company's uptime. With the expreZo™ EZswitch, you can access and control computers that require remote rebooting or troubleshooting, ensuring business continuity and minimizing expensive travel costs.

- Easy to install and setup
- All-in-one compact design
- Video resolution support of up to 2048 x 1536
- PS/2 and USB ports (keyboard and mouse) for local access



8- AND 16-PORT COMBO KVM SWITCH

FEATURES

Connect computers via PS/2 and/or USB

- Supports Windows, Linux, Mac OS9/OSX, Sun Microsystems
- On-Screen-Display (OSD) & Cascade Chain functions
- OSD with intuitive menus for quick and effective navigation
- Daisy chain switches to control up to 4096 PCs (16-Port) from a single console. Cascaded units do not need special configuration
- Hot-pluggable: all devices connected to expreZo can be added or removed at any time without shutting down the devices
- Auto Scan video for effortless monitoring
- Easily switch between connected devices with:
 - Hardware Push Button
 - Hot-Keys on PS/2 and/or USB keyboard
 - OSD menu
- Supports LED display for PC and/or server status monitoring
- Supports video resolutions up to 2048 x 1536
- Enable/disable beeper during channel switching
- Supports tiering with Dominion® KX2 models
- Rack mountable in 19" rack (1U)
- Firmware is upgradeable via a mini-USB port

SYSTEM REQUIREMENTS

Local Console

- Supports VGA, SVGA, Multisync monitor high resolution video – 2048x1536
- PS/2 and/or USB Keyboard/Mouse

Computer of Server

PCs must support:

- VGA, SVGA or Multisync card
- Type A USB port or mini-DIN 6 pin PS/2 keyboard and mouse

Cables

- EZ-116 – 16-port combo KVM
- One user
- 8 x 1.8m cables
- One US-type plug power adapter

EZSWITCH COMBO KVM SERIES SPECIFICATIONS

Models		EZ-108 (8-port) / EZ-116 (16-port)
Selection Method		Push Button and Hot-Key (PS/2 / USB Keyboard) Or On-Screen-Display (OSD)
LEDs		Red for PC Selection Green for PC On-Line ready
KVM Ports	Video (KB/MS)	8/16 x HDB-15 female [PS/2 & USB signal combined]
Console Ports	Keyboard Mouse Video Keyboard Mouse	1 x 6 pin mini-DIN female 1 x 6 pin mini-DIN female 1 x HDB-15 female 1 x USB – A type female 1 x USB – A type female
Auto-Scan Interval		Adjustable time setting by OSD menu driven
DDC, DDC2 Monitor		Max. Resolution up to 2048 x 1536 @ 65Hz
Hot Swappable		Yes
Operating Systems Supported		Windows 98SE/ME/2000/XP/2003/Vista/7 Server, Linux, Mac OS9/OSX and Sun Microsystems
Power		External power adapter, DC 5V, 2.0A
Dimensions (LxWxH)		17.3" x 6.1" x 1.5"; 44 x 15.7 x 4.5 cm
Unit Weight		3.86 lbs / 4.19 lbs; 1750g / 1900g
Housing Material		Metal
Operating Temperature		0–50°C; 2–122°F
Humidity		0%–80%RH
Firmware Upgrade Port		Mini USB female



Visit www.raritan.com/products/analog-kvm/exprZo
or Call 1.800.724.8090 for more information.

©2016 Raritan Inc. All rights reserved. Raritan® is a registered trademarks of Raritan Inc. or its wholly-owned subsidiaries. All others are registered trademarks or trademarks of their respective owners. Raritan began developing KVM switches for IT professionals to manage servers remotely in 1985. Today, as a brand of Legrand, we are a leading provider of intelligent rack PDUs. Our solutions increase the reliability and intelligence of data centers in 9 of the top 10 Fortune 500 technology companies. Learn more at Raritan.com **V1228**

Raritan®
A brand of  **legrand**